

## Accura<sup>®</sup> ClearVue<sup>™</sup> Free (SL 7870)

**Clear Class** 

High clarity plastic for a multitude of applications

## **Post-Cured Material**

MEASUREMENT	CONDITION	METRIC	U.S.
Tensile Strength (MPa/PSI)	ASTM D 638	38-42	5470-6050
Tensile Modulus (MPa/KSI)	ASTM D 638	1940-2250	281-326
Elongation at Break (%)	ASTM D 638	10-22	10-22
Flexural Strength (MPa/PSI)	ASTM D 790	73-76	10585-11020
Flexural Modulus (MPa/KSI)	ASTM D 790	1940-2250	281-326
Impact Strength (J/m /Ft-lbs/in)	ASTM D 256	23-51	0.43-0.96
Heat Deflection Temperature	ASTM D 648 @ 66 PSI @ 264 PSI	48 °C 41 °C	118 °F 106 °F
Coefficient of Thermal Expansion (CTE)	ASTM E 831-93 30-50 °C 70-140 °C	97 216	54 120
Water Absorption (%)	ASTM D 570-98	0.38	0.38
Glass Transition (Tg)	DMA, E"	56 °C	133 °F
Hardness, Shore D		86	86

## **Features**

- Clear and transparent
- · Rigid and tough
- Great for headlamps, bottles and transparent assemblies
- Excellent humidity/moisture resistance

## Liquid Material

MEASUREMENT	CONDITION	VALUE
Viscosity	@ 30 °C (86 °F)	180 cps
Penetration Depth (Dp)		7.2 mils
Critical Exposure (Ec)		10.6 mJ/cm <sup>2</sup>
Color		Clear
Solid Density	@ 25 °C (77 °F)	1.15 g/cm³
Liquid Density	@ 28 °C (82 °F)	1.13 g/cm³



www.3dsystems.com

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2017 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems and Accura are registered trademarks and ClearVue and the 3D Systems logo are trademarks of 3D Systems, Inc.